

HUWA-SAN FOGGER

Disinfects everywhere quickly and effectively

Huwa-San® Fogger is a solid, reliable and easy to use whole room disinfection device. It enables users to disinfect walls, floors, ceilings and other surfaces. Huwa-San® Fogger uses Huwa-San 12,5 MD (12,5% H_2O_2) and Huwa-San 7,9 MD (7,9% H_2O_2) as disinfectant, which meets the highest EN disinfection standards for bactericides, fungicides and virucides.

The device's excellent disinfection results, its clear digital display and its mobility make Huwa-San Fogger[©] the most intuitive and user-friendly option on the market today.

Stop Infection From Spreading

Science has shown that hospital acquired infections (HAI's) are not only transferred by other patients, but also by healthcare personnel or transmitted by water or air. The immediate environment of the patient can also be an important source of nosocomial infections and cross infections. Many micro-organisms (bacteria, but also viruses and spores) causing these infections (including MRSA & COVID-19) are known to contaminate the hospital environment and survive on dry surfaces for days, weeks and even months.

Contamination of frequent touch surfaces in healthcare settings are therefore an important source of viral transmission. Huwa-San Fogger[©]'s unrivaled performance will help in the prevention of further spread which is crucial to stop an outbreak and to control an infectious thread.

ADVANTAGES

- Efficient, fast, simple room disinfection technology
- Specially for surfaces that are high touch, low touch and surfaces that are difficult to reach
- Can be applied proactive, scheduled or in case of an outbreak
- Effective at ambient temperature and standard humidity
- Excellent material compatibility
- Eco-friendly » no residual (only water (H_2 0) and oxygen (O_2))





Medical support



KEY BENEFITS



Clinically proven action



Effective bactericide, fungicide, virucide & mycobactericide



No-rinse application



Disinfects high touch - low touch surfaces



Effective against coronaviruses



Leaves no odour and no colour

TECHNICAL SPECIFICATIONS

| HUWA-SAN [®] FOGGER | | | |
|------------------------------|---|-------------------------|--|
| GENERAL | | | |
| Model/Type reference | Huwa-San [©] Fogger | Tank Capacity Liquid | 11 Huwa-San TR-12,5 / 12,5 MD and Huwa-San TR-7,9 / 7,9 MD |
| Housing | Mixed materials: plastic case and metal sheets (IP20) | Bottle identification | Yes – RFID tag |
| Nozzle type | Venturi | Display | 5 Inch Resistive Touch Screen (800x480) |
| Connection to mains supply | Detachable power cord | CE-certification | Yes |
| SPECIFICATIONS | | | |
| Voltage | 230V AC | Weight of the equipment | Device without nozzle head, bottle and power cord: 9950g |
| Frequency | 50Hz | | |
| Dimensions of the equipment | 376x278x414 mm | | Nozzle head: 540g |
| Equipment mobility | Portable device | | Power cord: approx. 310g |
| OPERATIONS | | | |
| Operating conditions | Continuous | Process recordable | No |
| Disinfection method | Cold fogging | Warranty | 2 years |
| Maximum room size | 142 m ³ | Monitoring | Disinfection time |
| Timer | Countdown | | |





